

## KDC-1046 大容量低速离心机

Low speed centrifuge (脱帽离心机)



### Features:

- ★ Microcomputer control, LCD liquid crystal display(LCD).
- ★ Ac frequency conversion motor drive, quiet operation clean.
- ★ Offers nine ascending and descending rate selection mode; Offer ten kinds of working mode selection ,can free programming call.
- ★ Speed/centrifugal force can be set and double synchronous display screen.
- ★ Two optional timing mode: run statr timing and timing starts to set speed, easy to switch.
- ★ Door with double lock rod design, magnetic locks, electric door, more safety and reliable operation.
- ★ Centrifugal lay particular stress on tolerance up to 30 grams, no special load balancing.
- ★ Can change at any time in the operation of the parameters without downtime
- ★ Unique design of air exhaust temperature, low noise.

低速离心机

### 特性:

- ★ 微电脑控制、LCD 液晶显示
- ★ 交流变频电机驱动，运行宁静清洁
- ★ 提供 9 种升、降速率选择模式；提供 10 种工作模式选择，可自由编程、调用
- ★ 转速 / 离心力可相互设定、同步显示
- ★ 两种计时模式可选：运行开始计时和到达设定转速开始计时，切换方便
- ★ 门盖双挂杆设计、磁感应门锁，电动开门，运行更加安全可靠
- ★ 离心偏重容忍度最大可达 30 克，无需专门称重配平
- ★ 运行中可随时更改参数，无需停机
- ★ 独特的风冷排风设计，温升低、噪音小。

KDC-1046 技术指标

| KDC-1046 技术指标        |                                     |
|----------------------|-------------------------------------|
| 最高转速Max speed        | 4000rpm                             |
| 最大相对离心力Max RCF       | 3184 × g                            |
| 转速精度Speed accuracy   | ± 10rpm                             |
| 转子最大容量Rotor capacity | 124 × 真空采血管                         |
| 温升指标Temperature rise | ≤10℃（运行20 分钟）                       |
| 噪 音Noise             | ≤55dB                               |
| 定时范围Timer range      | 1min ~ 99:99:59（hh:mm:ss）/ 连续/ 短时离心 |
| 结 构Construction      | 钢制结构，不锈钢离心腔                         |
| 重 量Weight            | 90kg                                |
| 外形尺寸Dimensions       | 580 × 740 × 520mm（L × W × H）        |

KDC-1046 可选配的转头、提篮

|       | 最大转速(r/min) | 最大相对离心力(×g) | 转头容量(ml)    |
|-------|-------------|-------------|-------------|
| 脱帽离心机 | 4000        | 3184 × g    | 124 × 真空采血管 |